

TT1100-OHP Water Sensing Cable for Suspended Piping, Modular



nVent RAYCHEM TraceTek TT1100-XX-OHP is a range of fixed length water detecting cable intended for use on the bottom side of suspended or rack mounted pipe. The outer layer of the sensor cable is designed to act like a wick so that even small leaks are drawn into contact with the cable to assure detection. TT1100-OHP is also very useful in dirty areas where contamination can cause problems.

CARACTERÍSTICAS

Advanced technology: synthetic fiber braid, designed to wick water along the cable even when the water leak is dripping from a single small pin hole or crack

Simple and fast to install: strap directly to the pipe, eliminate drip trays

Easy to design: rapid drying, so that once the leak is located and repaired it will be ready for re-use

Distributed leak detection and location over a wide range of areas

ESPECIFICACIONES

Diámetro exterior:	8,2 mm
Max Operating Temperature:	80 °C
Detection Method:	Raychem Conductive-Polymer Technology
Model:	Sensing Cable
Detection:	Water

Table 1/1

Número de catálogo	Nombre del artículo	Longitud
P000000809	TT1100-OHP-15M-PC	15 m
P000000811	TT1100-OHP-3M-PC	3 m
P000000808	TT1100-OHP-30M-PC	30 m

Número de catálogo	Nombre del artículo	Longitud
P000000806	TT1100-OHP-100M-PC	100 m
P000000807	TT1100-OHP-50M-PC	50 m
P000001378	TT1100-OHP-5M-PC	5 m
P000000810	TT1100-OHP-7.5M-PC	7.5 m
P000000812	TT1100-OHP-1M-PC	1 m

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT