


Novastar Rear Panel With Cable Ducting

Servicios públicos de energía



Novastar Rear Panel with 3 U cable ducting for improved cable management.

CERTIFICACIONES



CARACTERÍSTICAS

Cable ducting and door hinge bracket

Cable ducting can be fitted at top or bottom

2 twist-locking catches (Torx T30, with 1/4 turn)

Incl. grounding

St, 1 mm

3 U cable ducting for cabinet heights 16, 20, 38, 47 U; 4 U cable ducting for cabinet heights 25, 34, 43 U

ESPECIFICACIONES

Table 1/2

Número de catálogo	Rack Height	Altura	Ancho	Color	Color Code	Product Type
25230-430	16 U	733 mm	553 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-430	16 U	733 mm	553 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-434	20 U	911 mm	553 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-434	20 U	911 mm	553 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-439	25 U	1133 mm	553 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-439	25 U	1133 mm	553 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-448	34 U	1534 mm	553 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-448	34 U	1534 mm	553 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-452	38 U	1711 mm	553 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-452	38 U	1711 mm	553 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-457	43 U	1933 mm	553 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-457	43 U	1933 mm	553 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-461	47 U	2111 mm	553 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-461	47 U	2111 mm	553 mm	Light Grey	RAL 7035	Cabinet/Rack Panel

Table 2/2

Número de catálogo	Tipo
25230-430	Rear Panel
26230-430	Rear Panel

Número de catálogo	Tipo
25230-434	Rear Panel
26230-434	Rear Panel
25230-439	Rear Panel
26230-439	Rear Panel
25230-448	Rear Panel
26230-448	Rear Panel
25230-452	Rear Panel
26230-452	Rear Panel
25230-457	Rear Panel
26230-457	Rear Panel
25230-461	Rear Panel
26230-461	Rear Panel

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE