

Packing Cap



Packing caps are used when splicing to short dowels and there is not enough room for standard installation equipment. Packing caps help retain and position packing materials, which helps minimize leakage of the molten filler materials during installation.

CARACTERÍSTICAS

Designed for specific sleeve and reinforcing bar combinations

Designed to fit over multiple reinforcing steel deformation and rib patterns

ESPECIFICACIONES

Material: Acero

Table 1/1

Número de catálogo	Tamaño de las barras de armado, métrico	Tamaño de las barras de armado, EE. UU.	Tamaño de armadura, Canadá	Diámetro 1 (Ø1)	Diámetro 2 (Ø2)
RBS362211	36 mm	#11	35 MILLONES	67 mm	44 mm
RBS362214	43 mm	#14	45 MILLONES	80 mm	54 mm
RBS362218	57 mm	#18	55 MILLONES	99 mm	67 mm
RBS36225	12 mm, 16 mm	#4, #5	10M, 15M	38 mm	19 mm
RBS36226	20 mm	#6	20M	41 mm	25 mm
RBS36227	22 mm	#7		44 mm	29 mm

Número de catálogo	Tamaño de las barras de armado, métrico	Tamaño de las barras de armado, EE. UU.	Tamaño de armadura, Canadá	Diámetro 1 (Ø1)	Diámetro 2 (Ø2)
RBS36228	25 mm	#8	25M	51 mm	32 mm
RBS36229	28 mm	#9	30M	57 mm	38 mm
RBS362210	32 mm	#10		60 mm	41 mm


DETALLES ADICIONALES DEL PRODUCTO

Contact nVent LENTON prior to purchasing. Metal caps should only be used by experienced installers.

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System Instruction Manual.

Sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

DIAGRAMAS



ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

+1.800.753.9221

Opción 1: Atención al
cliente

Opción 2: Soporte técnico

Europa

Países Bajos:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Alemania:

800 1890272

Otros países:

+31 13 5835404

Asia-Pacífico

Shanghái:

+86 21 2412 1618/19

Sídney:

+61 2 9751 8500



Nuestro gran portafolio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

©2025 nVent. Todas las marcas y logotipos de nVent son propiedad de nVent Services GmbH o sus filiales, o se utilizan bajo su licencia. El resto de las marcas comerciales son propiedad de sus respectivos propietarios. nVent se reserva el derecho a cambiar las especificaciones sin previo aviso.

Este documento lo ha generado el sistema.