

Guide Rail Accessories for Heavy PCBs, Extra Strong

Power Utilities



This reinforced guide rail for heavy PCBs of the type accessory, forms a reliable interface between the subrack mechanics and the sub-assemblies. The guide rails can additionally be bolted to the horizontal

CERTIFICACIONES



CARACTERÍSTICAS

For especially heavy PCBs, plug-in units or frame type plug-in units

Mounting, for bolting to type H (heavy) and type R (rugged) horizontal rails only

Aluminium profile

ESPECIFICACIONES

Table 1/2

Número de catálogo	Profundidad de la placa	Ancho de ranura	Color	Material	Familia de productos	Tipo de producto
--------------------	-------------------------	-----------------	-------	----------	----------------------	------------------

34562-884	340 mm	2	Plata	Aluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac	Guía de tren
34562-885	400 mm	2	Plata	Aluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac	Guía de tren
34562-881	160 mm	2	Plata	Aluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac	Guía de tren
34562-883	280 mm	2	Plata	Aluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac	Guía de tren
34562-882	220 mm	2	Plata	Aluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac	Guía de tren
34564-881	160 mm	2.5	Plata	Aluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac	Guía de tren

34564-882	220 mm	2.5	Plata	Aluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac	Guía de tren
34564-883	280 mm	2.5	Plata	Aluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac	Guía de tren
34564-884	340 mm	2.5	Plata	Aluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac	Guía de tren
34564-885	400 mm	2.5	Plata	Aluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac	Guía de tren

Table 2/2

Número de catálogo	Tipo	Compatible con
34562-884	Servicio pesado	Subpistas, Casos, Chasis
34562-885	Servicio pesado	Subpistas, Casos, Chasis
34562-881	Servicio pesado	Subpistas, Casos, Chasis
34562-883	Servicio pesado	Subpistas, Casos, Chasis
34562-882	Servicio pesado	Subpistas, Casos, Chasis

Número de catálogo	Tipo	Compatible con
34564-881	Servicio pesado	Subpistas, Casos, Chasis
34564-882	Servicio pesado	Subpistas, Casos, Chasis
34564-883	Servicio pesado	Subpistas, Casos, Chasis
34564-884	Servicio pesado	Subpistas, Casos, Chasis
34564-885	Servicio pesado	Subpistas, Casos, Chasis

DETALLES ADICIONALES DEL PRODUCTO

Delivery is exclusively in standard pack quantity.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestro gran portafolio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE