

GEHU Configured MI Heating Unit



nVent RAYCHEM Configured mineral insulated (MI) heating units are factory terminated and ready to install, providing freeze protection and process temperature maintenance on pipes/vessels. They incorporate both single and dual conductor cable mineral insulated cables, different sheath materials and a market leading range of resistances to cover an extensive range of design possibilities.

CARACTERÍSTICAS

Fast installation: factory-terminated and fully tested, eliminating risk of rework in field

Reliable during long life: 10 year product warranty available, robust and rugged construction, proven in harsh climates extends life expectancy

Reduced total installed cost

Dual conductor versions particularly suited to small pipes and instrument tubing

Reduced power supply costs: lower start up currents compared with other technologies

Simple controls: current monitoring on series resistance provides instant visibility on critical circuits

Fast track/expedited service for configured heating units for eligible designs

ESPECIFICACIONES

Table 1/2

Número de catálogo	Heating Cable Technology	Supply Voltage	Material aislante	Sheath Material	Outer Jacket Material	Area Classification
GEHU	Series Mineral Insulated	0 – 600 V	Magnesium Oxide	Alloy 825, Copper, Cupro-Nickel, SS321, Inconel 600	None, LSZH	Non-Hazardous, Hazardous

Table 2/2

Número de catálogo	Temperatura de instalación mín.
GEHU	-60 °C

ADDITIONAL PRODUCT DETAILS

Sheath Material: Cupro-Nickel, SS321 and Inconel 600 are not available in North America.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica
Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

**Europe, Middle East,
Africa**
Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific
Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latinoamérica
Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT