

# Reinforcing Steel Cleaning Brush



The reinforcing steel cleaning brush is used to prepare reinforcing steel for use with nVent LENTON Cadweld. The brush is designed to remove rust, mill scale, dirt and paint in as little as five seconds.

## CARACTERÍSTICAS

Designed for use with a 3/4", heavy duty, low-speed drill (200-350 rpm)

Cleans reinforcing steel bar, including the bar end

## ESPECIFICACIONES

**Material:** Acero

Table 1/1

| Número de catálogo | Tamaño de las barras de armado, métrico | Tamaño de las barras de armado, EE. UU. | Tamaño de armadura, Canadá | Diámetro (Ø) | Longitud (L) |
|--------------------|-----------------------------------------|-----------------------------------------|----------------------------|--------------|--------------|
| RBW34311           | 36 mm                                   | #11                                     | 35 MILLONES                | 114 mm       | 244mm        |
| RBW34318           | 57 mm                                   | #18                                     | 55 MILLONES                | 127 mm       | 206mm        |
| RBW34314           | 43 mm                                   | #14                                     | 45 MILLONES                | 127 mm       | 181mm        |

## DETALLES ADICIONALES DEL PRODUCTO

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

Brushes must be kept free of grease, oil and other contaminants that could evolve gas and cause porosity in the filler material.

Do not reverse the cleaning brush while it is engaged with the reinforcing steel bar.

Eye protection should be used when using power-driven cleaning brushes.

DIAGRAMAS



ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

+1.800.753.9221  
Opción 1: Atención al cliente  
Opción 2: Soporte técnico

Europa

Países Bajos:  
+31 800-0200135  
Francia:  
+33 800 901 793

Europa

Alemania:  
800 1890272  
Otros países:  
+31 13 5835404

Asia-Pacífico

Shanghái:  
+86 21 2412 1618/19  
Sídney:  
+61 2 9751 8500



Nuestro gran portafolio de marcas:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE