

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding

Servicios públicos de energía

Rear horizontal rail for backplane mounting with insulation strip



CERTIFICACIONES



CARACTERÍSTICAS

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version without front handles

Supplied as space-saving flat-pack

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Profundidad	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-161	3 U	175 mm	1	Backplane	160 mm	Textile
24563-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile
24563-461	6 U	175 mm	1	Backplane	160 mm	Textile
24563-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile

Table 2/3

Número de catálogo	Shock and Vibration Tolerance	Handle Included	Montaje	Cumple con	EMC Shielding	Product Type
24563-161	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-162	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-163	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-164	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-461	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-462	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-463	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis

Número de catálogo	Shock and Vibration Tolerance	HandleIncluded	Montaje	Cumple con	EMC Shielding	Product Type
24563-464	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis

Table 3/3

Número de catálogo	Rack Width	Carga estática
24563-161	84 HP	15 kgf
24563-162	84 HP	15 kgf
24563-163	84 HP	15 kgf
24563-164	84 HP	15 kgf
24563-461	84 HP	15 kgf
24563-462	84 HP	15 kgf
24563-463	84 HP	15 kgf
24563-464	84 HP	15 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE