

TT3000 Conductive Liquids Sensing Cable, Modular



nVent RAYCHEM TraceTek TT3000-XX-MC are a range of fixed length modular leak detection cables with metal connectors, used to detect spills and leaks of conductive liquids, including waste water, acids, bases and hazardous waste streams. Installed with an alarm and locating module, the cable senses aqueous chemical leaks, triggers an alarm and pinpoints the location. The cable is designed for a variety of applications, including floor surfaces, subfloors, equipment locations, pipes, storage tanks, and trenches.

CARACTERÍSTICAS

Advanced technology: conductive polymer & fluoropolymer construction, mechanically strong and resistant to chemicals

Simple and fast to install: small, lightweight and flexible

Easy to design

Distributed leak detection and location over a wide range of areas

Reliable and durable: 5 year product warranty available

ESPECIFICACIONES

Diámetro exterior:	6 mm
Max Operating Temperature:	85 °C
Detection:	Conductive Liquids and Aqueous Chemicals
Detection Method:	Raychem Conductive-Polymer Technology
Model:	Sensing Cable

Table 1/1

Número de catálogo	Nombre del artículo	Longitud
148983-000	TT3000-0.3M/1FT-MC	0.3 m
301795-000	TT3000-30M/100FT-MC	30 m
262789-000	TT3000-1.5M/5FT-MC	1.5 m

Número de catálogo	Nombre del artículo	Longitud
492017-000	TT3000-60M/200FT-MC	60 m
048179-000	TT3000-15M/50FT-MC	15 m
103619-000	TT3000-7.5M/25FT-MC	7.5 m
792293-000	TT3000-4.5M/15FT-MC	4.5 m
842667-000	TT3000-3M/10FT-MC	3 m

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT