

Shelf for air circuit-breakers (ACB) | Répartition de puissance, MSCC



The galvanised steel shelf, MSCC, covers a partial depth of an enclosure and is ideal for equipment requiring strong fixation, such as heavy air circuit breakers. It leaves the rear of the enclosure accessible for easy installation and wiring.

FONCTIONS

Description: Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette. The shelf has ventilation slots to allow air circulation in the section. It can be mounted only if we have internal side panels MSPSxx06 in both sides. Adjustable height position in steps of 25mm. It can not be used with the front covers system, if it is necessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections.

Matériau: 2 mm galvanised steel.

Livraison: 1 piece with mounting material.

Comprend le matériel de montage

In order to mount the shelf, internal side panels (MSPS), are required

Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette

The shelf has ventilation slots to allow air circulation in the section

It can be mounted only if we have internal side panels MSPSxx06 in both sides

Adjustable height position in steps of 25mm

d with the front covers system, if it is necessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections it can not be use

Includes mounting hardware

SPÉCIFICATIONS

Épaisseur: 2mm
Matériau: Acier doux
Finition: Plaqué

Table 1/1						
Référence catalogue	Hauteur	Largeur	Profondeur	Largeur de la platine de montage	Profondeur de montage maximale	Matériau de l'armoire
MSCC1006	78mm	1000mm	600mm	904mm	283mm	Acier doux
MSCC0606	78mm	600mm	600mm	504mm	283mm	Acier doux
MSCC0806	78mm	800mm	600mm	704mm	283mm	Acier doux

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.



Notre gamme complète de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE