

# TT-TS12 Alarm Panel



nVent RAYCHEM TraceTek TT-TS12 Touch Screen Panel provides a graphic user interface to manage and display information from a network of up to 250 external leak detection circuits. With interactive and dynamic leak location maps and displays, the leak location can be displayed on the floor plan, piping layout or photo of a single piece of equipment. Provides a quick status overview of all leak detection cables. Works with TTSIM or wireless mesh transmitters.

## CARACTERÍSTICAS

Easy to install, simple to set up and operate

Graphic display of leak location: 12" full color, high resolution SVGA touch screen display

Flexible interface options: audible alarm, summary relays, serial data and web interfaces are provided as standard

Onboard memory for up to 5000 events, simple off-line archiving and software updates

Available in various configurations

Email alerts allow 24/7 remote notification of an alarm

CE and UL 508 compliant

## ESPECIFICACIONES

|                                       |                                          |
|---------------------------------------|------------------------------------------|
| <b>Relay Contacts:</b>                | 8 Relays (4 System, 4 User Programmable) |
| <b>Display:</b>                       | 12" Touch Screen, TFT LCD                |
| <b>Profundidad:</b>                   | 54 mm                                    |
| <b>Altura:</b>                        | 237 mm                                   |
| <b>Ancho:</b>                         | 311 mm                                   |
| <b>Temperatura de funcionamiento:</b> | -20 a 60 °C                              |

Table 1/1

| Número de catálogo | Nombre del artículo | Number of TTSIM |
|--------------------|---------------------|-----------------|
| P000001487         | TT-TS12-PANEL-S1-1  | 1 x TTSIM-1     |
| P000001491         | TT-TS12-PANEL-S1A-1 | 1 x TTSIM-1A    |

| Número de catálogo | Nombre del artículo | Number of TTSIM |
|--------------------|---------------------|-----------------|
| P000001488         | TT-TS12-PANEL-S1-2  | 2 x TTSIM-1     |
| P000001492         | TT-TS12-PANEL-S1A-2 | 2 x TTSIM-1A    |
| P000001486         | TT-TS12-PANEL-0     | No              |
| P000001489         | TT-TS12-PANEL-S1-3  | 3 x TTSIM-1     |
| P000001490         | TT-TS12-PANEL-S1-4  | 4 x TTSIM-1     |
| P000001493         | TT-TS12-PANEL-S1A-3 | 3 x TTSIM-1A    |
| P000001494         | TT-TS12-PANEL-S1A-4 | 4 x TTSIM-1A    |

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

### Norteamérica

Tel +1.800.545.6258  
Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latinoamérica

Tel +1.713.868.4800  
Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**