


# nVent LENTON Interlok Form Saver Seal



The nVent LENTON Interlok Form Saver Seal provides an easy and efficient means for securing nVent LENTON Interlok Grout-Fill Coupler variants to formwork. Designed for cast-in-place applications, simply click and tap the Form Saver Seal into the coupler and utilize the sturdy mounting plate to fasten onto the formwork. The integrated seal allows the secondary rebar to be inserted into the coupler and prevents concrete paste contamination and grout leakage out of the cavity.

Interlok Grout-Fill Coupler variants can be used to splice steel bars in various cast-in-place applications. When combined with the Form Saver Seal, this powerful combination can be utilized for segmental pours, closure pours, post-tensioned slabs, and repair work.

## FONCTIONS

Sturdy, spring-steel mounting flange

Integrated rubber seal for grout cavity

Easy snap-in installation

Four keyholes for easy fastening using nails/screws

Anchor tabs prevent dislodging in concrete

Compatible with all nVent LENTON Interlok Grout-Fill Coupler variants

## SPÉCIFICATIONS

**Finition:** Brut

**Matériau:** Acier


Table 1/1

| Référence catalogue | Longueur (L) | Largeur (W) | Hauteur (H) | A | Couleur | Poids unitaire |
|---------------------|--------------|-------------|-------------|---|---------|----------------|
|---------------------|--------------|-------------|-------------|---|---------|----------------|

|         |         |         |        |         |       |        |
|---------|---------|---------|--------|---------|-------|--------|
| LKFSA25 | 101.6mm | 113.6mm | 10.2mm | 85.2 mm | Rouge | 0.1 kg |
| LKFSA22 | 101.6mm | 113.6mm | 10.2mm | 85.2 mm | Bleu  | 0.1 kg |
| LKFSA20 | 101.6mm | 113.6mm | 10.2mm | 85.2 mm | Jaune | 0.1 kg |
| LKFSA16 | 101.6mm | 113.6mm | 10.2mm | 85.2 mm | Noir  | 0.1 kg |

| Accessory Part Number | Compatible With:                                   |                                                       |
|-----------------------|----------------------------------------------------|-------------------------------------------------------|
|                       | Interlok Standard Grout Filled Couplers(LK Series) | Interlok No-Thread Grout Filled Couplers(LKNT Series) |
| LKFSA16               | LK16, LK16D                                        | -                                                     |
| LKFSA20               | LK20(D)                                            | LKNT20(D)                                             |
| LKFSA22               | LK5, LK6, LK7, LK22(D)                             | LKNT22(D)                                             |
| LKFSA25               | LK8, LK25(D)                                       | LKNT25(D)                                             |

## DIAGRAMMES



## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur [www.nvent.com](http://www.nvent.com) et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Notre gamme complète de marques:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**