

# Horizontal Rail Insulation Strip

## Centrale d'électricité



Strip enables an insulated mounting of backplanes or metal plates as supports for connectors. Creates standardized mounting depth for plug-in units in the subrack in conjunction with L-ST and H-ST horizontal rails. Suitable for RatiopacPRO/-AIR, Propac Pro, CompacPRO and EuropacPRO/-Rugged.

### CERTIFICATIONS



### CARACTÉRISTIQUES

For insulated mounting of backplanes or metal plates as supports for connectors

Creates standardised mounting depth for plug-in units in the subrack in conjunction with L-ST and H-ST horizontal rails

### LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2

| Référence catalogue | Rack Width | Package Quantity | Indice d'inflammabilité | Longueur | Matériau      | Product Family                                                        |
|---------------------|------------|------------------|-------------------------|----------|---------------|-----------------------------------------------------------------------|
| 24560-820           | 20 HP      | 10               | UL® 94V-0               | 101.5 mm | Polycarbonate | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac |

| Référence catalogue | Rack Width | Package Quantity | Indice d'inflammabilité | Longueur  | Matériau      | Product Family                                                        |
|---------------------|------------|------------------|-------------------------|-----------|---------------|-----------------------------------------------------------------------|
| 24560-863           | 63 HP      | 10               | UL® 94V-0               | 316.88 mm | Polycarbonate | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac |
| 24560-842           | 42 HP      | 10               | UL® 94V-0               | 210.4 mm  | Polycarbonate | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac |
| 24560-884           | 84 HP      | 10               | UL® 94V-0               | 428.64 mm | Polycarbonate | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac |
| 24560-828           | 28 HP      | 10               | UL® 94V-0               | 144.2 mm  | Polycarbonate | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac |
| 24560-840           | 40 HP      | 10               | UL® 94V-0               | 205.12 mm | Polycarbonate | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac |

Table 2/2

| Référence catalogue | Product Type     | Fonctionne avec |
|---------------------|------------------|-----------------|
| 24560-820           | Insulation Strip | Subracks, Cases |
| 24560-863           | Insulation Strip | Subracks, Cases |
| 24560-842           | Insulation Strip | Subracks, Cases |

| Référence catalogue | Product Type     | Fonctionne avec |
|---------------------|------------------|-----------------|
| 24560-884           | Insulation Strip | Subracks, Cases |
| 24560-828           | Insulation Strip | Subracks, Cases |
| 24560-840           | Insulation Strip | Subracks, Cases |

## ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : [www.nvent.com](http://www.nvent.com) et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**