

Polymer Junction Box For PI Cables



nVent RAYCHEM JB-EX-XX are junction boxes with or without earth plate and external earth stud. Depending on the type, they are equipped with 10 mm² or 35 mm² terminals to allow loads up to 100 A to a power supply or other configurations such as Tees or Splices. Available in different sizes with a various number of M20 entries to accommodate multiple configurations and electrical loads.

CARACTERÍSTICAS

Simple and fast to install, easy to maintain

Hazardous areas approved

Available in different models and sizes for multiple configurations

Reliable during long life: 10 year product warranty available, maintenance free

ESPECIFICACIONES

Area Classification:	Non-Hazardous; Hazardous
Clasificación IP:	IP66
Montaje:	Wall/Support Bracket Mounted
Ambient Temperature:	-55 a 55 °C

Table 1/2

Número de catálogo	Nombre del artículo	Max Voltage	Cable Entry	Max Conductor Cross Section	Altura	Ancho
1244-006384	JB-EX-20-EP	590 V	1xM25 3xM20	10 mm ²	120 mm	122 mm
1244-000579	JB-EX-21	550 V	1xM32 6xM20	10 mm ²	160 mm	160 mm
1244-000590	JB-EX-20	590 V	1xM25 3xM20	10 mm ²	120 mm	122 mm
1244-006653	JB-EX-21/35MM2	690 V	1xM40 6xM20	35 mm ²	160 mm	260 mm

Table 2/2

Número de catálogo	Nombre del artículo	Profundidad	Light Indication Included	Earth Plate Included
1244-006384	JB-EX-20-EP	90 mm	No	Sí
1244-000579	JB-EX-21	90 mm	No	No
1244-000590	JB-EX-20	90 mm	No	No
1244-006653	JB-EX-21/35MM2	90 mm	No	No

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT