

T2Red Self-Regulating Floor Heating Cable With Spooling System



nVent RAYCHEM T2Red is a self-regulating floor heating cable for new build and renovation. It can be applied under any type of floor surface without risk of overheating. Ideal for natural stone and ceramic tiles, also temperature sensitive floors such as wood and laminate. The T2Red packs include the elegant and user-friendly SENZ WIFI touchscreen thermostat and all accessories needed to install of the floor heating system (installation manuals, commissioning sheet, glue sticks, sensor tube and floor sensor).

CARACTERÍSTICAS

Energy efficient and self regulating: automatically adjusts heat output, more heat near windows, less heat under furnishings

Increased comfort when used with T2Reflecta insulation board: heat spreads perfectly over the entire room

Simple, fast installation: cut-to-length, no cold leads, ideal for complex floor plans, suitable for all sub-floors and floor coverings, meter markings, user-friendly connection kits

Safe and efficient operation: fast heat up, flexible power output from 50-100W/m², closer loops for higher output and wider loops for lower output, no overheating

EcoDesign compatible kits including the energy efficient and advanced SENZ WIFI touchscreen thermostat that can be controlled through the SENZ WIFI app or through voice control using Alexa or Google Assistant compatible smartspeakers.

Reliable during long life: 12 to 20 year total care warranty available, no maintenance required

ESPECIFICACIONES

Temperatura de instalación mín.:	5 °C
Power Output:	5 – 15 W/m
Nominal Height:	5,8 mm
Nominal Width:	8,5 mm
Nominal Cable Weight:	68 g/m
Power Output, Typical:	80 – 125 W/m ²
Max Circuit Length:	100 m
Tensión nominal:	230 V
Ground Path Type:	Trenzado
Outer Jacket Material:	Fluoropolímero

Color:	Rojo
Heating Cable Technology:	Self-Regulating
Thermostat Included:	SENZ-WIFI
Circuit Breaker:	Type C/10Amp
Spooling System:	Sí

Table 1/1

Número de catálogo	Nombre del artículo	Energía	Longitud
1244-022586	R-RD-B-16M/SENZ-WIFI	160 W	16 m
1244-022587	R-RD-B-23M/SENZ-WIFI	245 W	23 m
1244-022588	R-RD-B-30M/SENZ-WIFI	320 W	30 m
1244-022589	R-RD-B-37M/SENZ-WIFI	400 W	37 m
1244-022590	R-RD-B-44M/SENZ-WIFI	480 W	44 m
1244-022591	R-RD-B-58M/SENZ-WIFI	640 W	58 m
1244-022592	R-RD-B-72M/SENZ-WIFI	800 W	72 m
1244-022593	R-RD-B-86M/SENZ-WIFI	960 W	86 m
1244-022594	R-RD-B-100M/SENZ-WIFI	1120 W	100 m

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT