

RackPower PDU, RP6xxx, 230/400 VAC, 3-phase

Centrale d'électricité

Modular, compact intelligent PDU with inlet metering and remote outlet switching. Ultra-Low Profile Design with only 50 mm height.

CARACTÉRISTIQUES

RackPower RP6xxx Intelligent Power Distribution Units monitors input and outlet power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6", with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

User-defined power-on time delay or automatic power-on sequencing

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2

Référence catalogue	Product Type	Socket Type	Couleur	Longueur	Tension CA	Fonction
RP6950	Socket Strip	IEC C13, IEC C13/C19	Noir	1826 mm	230 V	Input Monitored, Outlet Monitored, Switched Outlets

Référence catalogue	Product Type	Socket Type	Couleur	Longueur	Tension CA	Fonction
RP6850	Socket Strip	IEC C13, IEC C13/C19	Noir	1780 mm	230 V	Input Monitored, Outlet Monitored, Switched Outlets
RP6450	Socket Strip	IEC C13, IEC C13/C19	Noir	1490 mm	230 V	Input Monitored, Outlet Monitored, Switched Outlets

Table 2/2

Référence catalogue	Profondeur	Largeur
RP6950	75 mm	56 mm
RP6850	75 mm	56 mm
RP6450	75 mm	56 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE