

Varistar CP IP 20 Cabinet, Glass Front Door, Steel Rear Door

Servicios públicos de energía

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

CARACTERÍSTICAS

Type of protection IP 20

With glass front door

Doors with single point locking, side panels with quick release fastener

Static load-carrying capacity 1600 kg

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Altura	Frame Color	Ancho	Frame Color Code	Cladding Material
10630-038	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Acero
10630-037	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Acero
10630-039	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Acero
10630-040	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Acero

Table 2/3

Número de catálogo	Profundidad	Cladding Color	Cladding Color Code	Cumple con	Frame Material	Product Type
--------------------	-------------	----------------	---------------------	------------	----------------	--------------

10630-038	800 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Acero	Gabinete
10630-037	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Acero	Gabinete
10630-039	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Acero	Gabinete
10630-040	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Acero	Gabinete

Table 3/3

Número de catálogo	Protection Rating	Carga estática
10630-038	IP20	1600 kgf
10630-037	IP20	1600 kgf
10630-039	IP20	1600 kgf
10630-040	IP20	1600 kgf

ADDITIONAL PRODUCT DETAILS

Lever handle can be added to the doors.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE