


Guide Rail With DIN Connector Fixing

Power Utilities



The the standard type guide rail with connector fixing allows the user to clip the DIN connectors directly onto the guide rails. Only applicable with Euroboards with the dimensions 100 x 160 mm and 100 x 220 mm. Suitable for RatiopacPRO/-AIR, PropacPRO, CompacPRO and EuropacPRO.

CERTIFICATIONS



FONCTIONS

Easy and economic mounting of connectors through snap connections as alternative to z-rails or horizontal rails with integrated z-rail

For single Euroboard format 100 × 160 mm or 100 × 220 mm; not suitable for double Euroboard format

Plastic guide rail, one piece, red, for 2 mm groove width

Can be clipped into horizontal rails in Al extrusion

Can be clipped into 1.5 mm thick plate

Storage temperature: from -40 °C ... 130 °C

SPÉCIFICATIONS

Table 1/2

Référence catalogue	Quantité par colis	Profondeur de la carte	Largeur de rainure	Couleur	Matériau	Famille de produits
---------------------	--------------------	------------------------	--------------------	---------	----------	---------------------

64560-075	1	220 mm	2	Rouge	Plastique	EuropacPRO, RatiopacPRO, RatiopacPRO Air, CompacPRO, PropacPRO, MultipacPRO, Inpac
64560-074	1	160 mm	2	Rouge	Plastique	EuropacPRO, RatiopacPRO, RatiopacPRO Air, CompacPRO, PropacPRO, MultipacPRO, Inpac

Table 2/2

Référence catalogue	Type de produit	Type	Compatible avec	Unité du colis
64560-075	Support de guidage	Standard avec connecteur DIN	Bacs à cartes, Coffrets, Châssis	Paire
64560-074	Support de guidage	Standard avec connecteur DIN	Bacs à cartes, Coffrets, Châssis	Paire

INFORMATIONS PRODUIT COMPLÉMENTAIRES

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.



Notre gamme complète de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE