


EuropacPRO Mounting Plate for Use With Cover Plate

Servicios públicos de energía



Mounting plate for use with cover plates for installation and fixing of heavy components. Full width mounting plates (as wide as the subrack or the system case) are fixed to the side panels. The partial width mounting plates are fixed to the side panel and horizontal rail by means of an assembly strip.

Guide rails Type 4,4" and type strengthened cannot be used in combination with a mounting plate. Top / bottom cover which will be inserted into the groove of the light (type L) horizontal rails cannot be used in combination with a mounting plate.

CERTIFICACIONES



CARACTERÍSTICAS

For installation and fixing of heavy components

Mounting plate, full width: The mounting plate is as wide as the subrack/system case and is fixed to the side panels

A guide rail can be fitted in first and last slot position

In addition to the mounting plate EMC cover plates can also be fitted to the subrack

Guide rails type 4.4 and "strengthened" cannot be used

ESPECIFICACIONES

Table 1/2

Número de catálogo	Rack Width	Package Quantity	Profundidad	Material	Product Family	Product Type
34563-004	84 HP	1	112.5 mm	Aluminio	EuropacPRO	Mounting Plate

Número de catálogo	Rack Width	Package Quantity	Profundidad	Material	Product Family	Product Type
34563-024	84 HP	1	172.5 mm	Aluminio	EuropacPRO	Mounting Plate
34563-026	84 HP	1	232.5 mm	Aluminio	EuropacPRO	Mounting Plate
34563-028	84 HP	1	292.5 mm	Aluminio	EuropacPRO	Mounting Plate
34563-042	84 HP	1	352.5 mm	Aluminio	EuropacPRO	Mounting Plate
34563-044	84 HP	1	412.5 mm	Aluminio	EuropacPRO	Mounting Plate
34563-001	28 HP	1	112.5 mm	Aluminio	EuropacPRO	Mounting Plate
34563-002	42 HP	1	112.5 mm	Aluminio	EuropacPRO	Mounting Plate
34563-003	63 HP	1	112.5 mm	Aluminio	EuropacPRO	Mounting Plate
34563-009	28 HP	1	172.5 mm	Aluminio	EuropacPRO	Mounting Plate
34563-014	42 HP	1	172.5 mm	Aluminio	EuropacPRO	Mounting Plate
34563-019	63 HP	1	172.5 mm	Aluminio	EuropacPRO	Mounting Plate

Table 2/2			
Número de catálogo	Ancho	Works With	Certificaciones
34563-004	431.35 mm	Subracks	RoHS
34563-024	431.35 mm	Subracks	RoHS
34563-026	431.35 mm	Subracks	
34563-028	431.35 mm	Subracks	
34563-042	431.35 mm	Subracks	
34563-044	431.35 mm	Subracks	

Número de catálogo	Ancho	Works With	Certificaciones
34563-001	146.88 mm	Subracks	RoHS
34563-002	217.99 mm	Subracks	RoHS
34563-003	324.67 mm	Subracks	RoHS
34563-009	146.88 mm	Subracks	RoHS
34563-014	217.99 mm	Subracks	RoHS
34563-019	324.67 mm	Subracks	RoHS

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE