

EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

Centrale d'électricité

Non-EMC shielded subrack for backplane mounting, light version.



CERTIFICATIONS



CARACTÉRISTIQUES

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2

Référence catalogue	Rack Height	Profondeur	Package Quantity	For Mounting	Board Depth	Handle Included
24564-131	3 U	175 mm	1	Carte fond de panier	160 mm	Non
24564-132	3 U	235 mm	1	Carte fond de panier	160 mm, 220 mm	Non
24564-133	3 U	295 mm	1	Carte fond de panier	160 mm, 220 mm, 280 mm	Non
24564-431	6 U	175 mm	1	Carte fond de panier	160 mm	Non
24564-432	6 U	235 mm	1	Carte fond de panier	160 mm, 220 mm	Non
24564-433	6 U	295 mm	1	Carte fond de panier	160 mm, 220 mm, 280 mm	Non

Table 2/2

Référence catalogue	Montage	Conformité à	EMC Shielding	Product Type	Rack Width	Charge statique
24564-131	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Non	Subrack/Chassis	84 HP	7.5 kgf
24564-132	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Non	Subrack/Chassis	84 HP	7.5 kgf
24564-133	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Non	Subrack/Chassis	84 HP	7.5 kgf
24564-431	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Non	Subrack/Chassis	84 HP	7.5 kgf
24564-432	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Non	Subrack/Chassis	84 HP	7.5 kgf
24564-433	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Non	Subrack/Chassis	84 HP	7.5 kgf

ADDITIONAL PRODUCT DETAILS

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE