

# TT1100-OHP-THIN Water Sensing Cable for Insulated Pipe, Modular



nVent RAYCHEM TraceTek TT1100-OHP-THIN is a range of fixed length, small diameter water sensing cables for use on insulated pipes.

## CARACTERÍSTICAS

Advanced technology: supplied with a porous fluoropolymer outer fiber braid surrounding the base TT1100 sensor cable

Simple and fast to install: the fiber overbraid provides superior flexibility, with factory fitted plastic connectors

Easy to design: modular, fixed lengths

Mechanically strong: fluoropolymer outer braid withstands compression forces associated with the use of sheet metal lagging surrounding the pipe insulation

## ESPECIFICACIONES

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| <b>Diámetro exterior:</b>         | 6,8 mm                                |
| <b>Max Operating Temperature:</b> | 80 °C                                 |
| <b>Detection Method:</b>          | Raychem Conductive-Polymer Technology |
| <b>Model:</b>                     | Sensing Cable                         |
| <b>Detection:</b>                 | Water                                 |

Table 1/1

| Número de catálogo | Nombre del artículo     | Longitud |
|--------------------|-------------------------|----------|
| P000001251         | TT1100-OHP-THIN-100M-PC | 100 m    |
| P000001252         | TT1100-OHP-THIN-50M-PC  | 50 m     |
| P000001253         | TT1100-OHP-THIN-30M-PC  | 30 m     |

## ADVERTENCIA

---

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

### Norteamérica

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latinoamérica

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**