

# T-Series Vertical Transition Filler Material Kit



T-Series vertical filler material kits contain the following: Filler material, two vertical packings, pouring basin ceramic guide tube and pouring basin crucible ceramic and disk. All filler material kits contain one-time use components that are sized to a specific sleeve, pouring basin and pouring basin crucible combination. Ordering filler material kits simplifies ordering, reduces order errors and helps ensure proper sizing of components.

## FONCTIONS

Simplifies ordering

Used to splice different diameter bars

All components are for one-time use

## SPÉCIFICATIONS

Table 1/1

| Référence catalogue | Taille de barre d'armature, métrique | Taille de barre d'armature, US | Taille de barre d'armature, Canada |
|---------------------|--------------------------------------|--------------------------------|------------------------------------|
| RBT911101B          | 36 mm, 28 mm                         | #11, #9                        | 35M, 30M                           |
| RBT910101B          | 32 mm, 28 mm                         | #10, #9                        |                                    |
| RBT1114101B         | 43 mm, 36 mm                         | #14, #11                       | 45M, 35M                           |
| RBT1118101B         | 57 mm, 36 mm                         | #18, #11                       | 55M, 35M                           |
| RBT1011101B         | 36 mm, 32 mm                         | #11, #10                       |                                    |
| RBT1418101B         | 57 mm, 43 mm                         | #18, #14                       | 55M, 45M                           |

## INFORMATIONS PRODUIT COMPLÉMENTAIRES


Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

Filler material kits are a component in splice kits. Care should be taken to avoid duplication of orders.

Components can also be purchased separately: (1) Filler Material, (2) Vertical Top Packing, (3) Vertical Bottom Packing, (4) Pouring Basin Ceramic Guide Tube, and (5) Crucible Ceramic and Disk.

| Filler Material Kit Components |                 |                      |                                       |                                  |
|--------------------------------|-----------------|----------------------|---------------------------------------|----------------------------------|
| Filler Material Kit            | Filler Material | Packing (2 Required) | Pouring Basin Ceramic Insert and Disk | Pouring Basin Ceramic Guide Tube |
| RBT910101B                     | RBF105          | RBS354712 RBS35475.5 | RBS5037                               | RBS5038                          |
| RBT911101B                     | RBF125          | RBS354714 RBS35476   | RBS5037                               | RBS5038                          |
| RBT1011101B                    | RBF125          | RBS354712 RBS35476   | RBS5037                               | RBS5038                          |
| RBT1114101B                    | RBF125          | RBS354715 RBS35476   | RBS5037                               | RBS5039                          |
| RBT1118101B                    | RBF240          | RBS354712 RBS354720  | RBS5037                               | RBS5039                          |
| RBT1418101B                    | RBF195          | RBS354720 RBS35477   | RBS5037                               | RBS5039                          |

## DIAGRAMMES



## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur [www.nvent.com](http://www.nvent.com) et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Notre gamme complète de marques:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**