


EuropacPRO Mounting Plate for Use With Cover Plate

Centrale d'électricité



Mounting plate for use with cover plates for installation and fixing of heavy components. Full width mounting plates (as wide as the subrack or the system case) are fixed to the side panels. The partial width mounting plates are fixed to the side panel and horizontal rail by means of an assembly strip.

Guide rails Type 4,4" and type strengthened cannot be used in combination with a mounting plate. Top / bottom cover which will be inserted into the groove of the light (type L) horizontal rails cannot be used in combination with a mounting plate.

CERTIFICATIONS



CARACTÉRISTIQUES

For installation and fixing of heavy components

Mounting plate, full width: The mounting plate is as wide as the subrack/system case and is fixed to the side panels

A guide rail can be fitted in first and last slot position

In addition to the mounting plate EMC cover plates can also be fitted to the subrack

Guide rails type 4.4 and "strengthened" cannot be used

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2

Référence catalogue	Rack Width	Package Quantity	Profondeur	Matériau	Product Family	Product Type
34563-019	63 HP	1	172.5 mm	Aluminium	EuropacPRO	Mounting Plate

Référence catalogue	Rack Width	Package Quantity	Profondeur	Matériau	Product Family	Product Type
34563-001	28 HP	1	112.5 mm	Aluminium	EuropacPRO	Mounting Plate
34563-003	63 HP	1	112.5 mm	Aluminium	EuropacPRO	Mounting Plate
34563-044	84 HP	1	412.5 mm	Aluminium	EuropacPRO	Mounting Plate
34563-042	84 HP	1	352.5 mm	Aluminium	EuropacPRO	Mounting Plate
34563-009	28 HP	1	172.5 mm	Aluminium	EuropacPRO	Mounting Plate
34563-002	42 HP	1	112.5 mm	Aluminium	EuropacPRO	Mounting Plate
34563-028	84 HP	1	292.5 mm	Aluminium	EuropacPRO	Mounting Plate
34563-026	84 HP	1	232.5 mm	Aluminium	EuropacPRO	Mounting Plate
34563-014	42 HP	1	172.5 mm	Aluminium	EuropacPRO	Mounting Plate
34563-024	84 HP	1	172.5 mm	Aluminium	EuropacPRO	Mounting Plate
34563-004	84 HP	1	112.5 mm	Aluminium	EuropacPRO	Mounting Plate

Table 2/2			
Référence catalogue	Largeur	Fonctionne avec	Certifications
34563-019	324.67 mm	Bacs à cartes	RoHS
34563-001	146.88 mm	Bacs à cartes	RoHS
34563-003	324.67 mm	Bacs à cartes	RoHS
34563-044	431.35 mm	Bacs à cartes	
34563-042	431.35 mm	Bacs à cartes	
34563-009	146.88 mm	Bacs à cartes	RoHS

Référence catalogue	Largeur	Fonctionne avec	Certifications
34563-002	217.99 mm	Bacs à cartes	RoHS
34563-028	431.35 mm	Bacs à cartes	
34563-026	431.35 mm	Bacs à cartes	
34563-014	217.99 mm	Bacs à cartes	RoHS
34563-024	431.35 mm	Bacs à cartes	RoHS
34563-004	431.35 mm	Bacs à cartes	RoHS

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE