

Front Panel, Front Anodized, Rear Conductive, Unshielded

Servicios públicos de energía

Front panel, unshielded, front anodized and rear conductive.



CERTIFICACIONES



CARACTERÍSTICAS

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Rack Width	Package Quantity	Handle Type	Montaje	Front Finish
30847-469	5 U	84 HP	1	Ninguno	Screw-on Front	Anodizado
30847-459	2 U	42 HP	1	Ninguno	Screw-on Front	Anodizado

Número de catálogo	Rack Height	Rack Width	Package Quantity	Handle Type	Montaje	Front Finish
30847-460	2 U	63 HP	1	Ninguno	Screw-on Front	Anodizado
30847-467	5 U	42 HP	1	Ninguno	Screw-on Front	Anodizado
30847-468	5 U	63 HP	1	Ninguno	Screw-on Front	Anodizado
30847-458	2 U	28 HP	5	Ninguno	Screw-on Front	Anodizado
30838-043	3 U	4 HP	5	Ninguno	Screw-on Front	Anodizado
30847-462	4 U	28 HP	5	Ninguno	Screw-on Front	Anodizado
30847-466	5 U	28 HP	5	Ninguno	Screw-on Front	Anodizado

Table 2/3						
Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
30847-469	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4 mm	Aluminio
30847-459	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	84 mm	Aluminio
30847-460	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	84 mm	Aluminio
30847-467	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4 mm	Aluminio
30847-468	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4 mm	Aluminio
30847-458	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	84 mm	Aluminio
30838-043	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio

Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
30847-462	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9 mm	Aluminio
30847-466	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4 mm	Aluminio

Table 3/3

Número de catálogo	Product Type	Tipo	Ancho	Certificaciones
30847-469	Front Panel	Front Panel without Handle	426.4 mm	
30847-459	Front Panel	Front Panel without Handle	213 mm	
30847-460	Front Panel	Front Panel without Handle	319.7 mm	
30847-467	Front Panel	Front Panel without Handle	213 mm	
30847-468	Front Panel	Front Panel without Handle	319.7 mm	
30847-458	Front Panel	Front Panel without Handle	141.9 mm	
30838-043	Front Panel	Front Panel without Handle	20 mm	RoHS
30847-462	Front Panel	Front Panel without Handle	141.9 mm	
30847-466	Front Panel	Front Panel without Handle	141.9 mm	

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE