

# Varistar CP Flat Top Cover Closed

## Servicios públicos de energía

Flat top cover for Varistar CP cabinets without cable entry zones.

### CARACTERÍSTICAS

Flat top cover closed

### ESPECIFICACIONES

Table 1/2

| Número de catálogo | Ancho  | Profundidad | Protection Rating | Color      | Color Code | Acabado                |
|--------------------|--------|-------------|-------------------|------------|------------|------------------------|
| 21630-260          | 600 mm | 300 mm      | IP20              | Black Grey | RAL 7021   |                        |
| 21630-315          | 600 mm | 300 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-557          | 600 mm | 300 mm      | IP55              | Black Grey | RAL 7021   |                        |
| 21630-570          | 600 mm | 300 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-128          | 600 mm | 1000 mm     | IP20              | Black Grey | RAL 7021   |                        |
| 21630-129          | 600 mm | 1100 mm     | IP20              | Black Grey | RAL 7021   |                        |
| 21630-130          | 600 mm | 1200 mm     | IP20              | Black Grey | RAL 7021   |                        |
| 21630-186          | 600 mm | 600 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-187          | 600 mm | 800 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |

| Número de catálogo | Ancho  | Profundidad | Protection Rating | Color      | Color Code | Acabado                |
|--------------------|--------|-------------|-------------------|------------|------------|------------------------|
| 21630-188          | 600 mm | 900 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-189          | 600 mm | 1000 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-190          | 600 mm | 1100 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-191          | 600 mm | 1200 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-254          | 600 mm | 600 mm      | IP20              | Black Grey | RAL 7021   |                        |
| 21630-255          | 600 mm | 800 mm      | IP20              | Black Grey | RAL 7021   |                        |
| 21630-256          | 600 mm | 900 mm      | IP20              | Black Grey | RAL 7021   |                        |
| 21630-558          | 600 mm | 600 mm      | IP55              | Black Grey | RAL 7021   |                        |
| 21630-559          | 600 mm | 800 mm      | IP55              | Black Grey | RAL 7021   |                        |
| 21630-560          | 600 mm | 900 mm      | IP55              | Black Grey | RAL 7021   |                        |
| 21630-561          | 600 mm | 1000 mm     | IP55              | Black Grey | RAL 7021   |                        |
| 21630-562          | 600 mm | 1100 mm     | IP55              | Black Grey | RAL 7021   |                        |
| 21630-563          | 600 mm | 1200 mm     | IP55              | Black Grey | RAL 7021   |                        |
| 21630-571          | 600 mm | 600 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-572          | 600 mm | 800 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-573          | 600 mm | 900 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-574          | 600 mm | 1000 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-575          | 600 mm | 1100 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |

| Número de catálogo | Ancho  | Profundidad | Protection Rating | Color      | Color Code | Acabado                |
|--------------------|--------|-------------|-------------------|------------|------------|------------------------|
| 21630-576          | 600 mm | 1200 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-192          | 800 mm | 600 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-257          | 800 mm | 600 mm      | IP20              | Black Grey | RAL 7021   |                        |
| 21630-564          | 800 mm | 600 mm      | IP55              | Black Grey | RAL 7021   |                        |
| 21630-577          | 800 mm | 600 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-131          | 800 mm | 1000 mm     | IP20              | Black Grey | RAL 7021   |                        |
| 21630-132          | 800 mm | 1100 mm     | IP20              | Black Grey | RAL 7021   |                        |
| 21630-133          | 800 mm | 1200 mm     | IP20              | Black Grey | RAL 7021   |                        |
| 21630-193          | 800 mm | 800 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-194          | 800 mm | 900 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-195          | 800 mm | 1000 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-196          | 800 mm | 1100 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-197          | 800 mm | 1200 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-258          | 800 mm | 800 mm      | IP20              | Black Grey | RAL 7021   |                        |
| 21630-259          | 800 mm | 900 mm      | IP20              | Black Grey | RAL 7021   |                        |
| 21630-565          | 800 mm | 800 mm      | IP55              | Black Grey | RAL 7021   |                        |
| 21630-566          | 800 mm | 900 mm      | IP55              | Black Grey | RAL 7021   |                        |
| 21630-567          | 800 mm | 1000 mm     | IP55              | Black Grey | RAL 7021   |                        |

| Número de catálogo | Ancho  | Profundidad | Protection Rating | Color      | Color Code | Acabado                |
|--------------------|--------|-------------|-------------------|------------|------------|------------------------|
| 21630-568          | 800 mm | 1100 mm     | IP55              | Black Grey | RAL 7021   |                        |
| 21630-569          | 800 mm | 1200 mm     | IP55              | Black Grey | RAL 7021   |                        |
| 21630-578          | 800 mm | 800 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-579          | 800 mm | 900 mm      |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-580          | 800 mm | 1000 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-581          | 800 mm | 1100 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |
| 21630-582          | 800 mm | 1200 mm     |                   | Black Grey | RAL 7021   | Recubrimiento de polvo |

| Table 2/2          |          |                        |        |             |
|--------------------|----------|------------------------|--------|-------------|
| Número de catálogo | Material | Product Type           | Tipo   | Works With  |
| 21630-260          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-315          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-557          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-570          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-128          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-129          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-130          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-186          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-187          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-188          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |

| Número de catálogo | Material | Product Type           | Tipo   | Works With  |
|--------------------|----------|------------------------|--------|-------------|
| 21630-189          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-190          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-191          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-254          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-255          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-256          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-558          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-559          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-560          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-561          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-562          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-563          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-571          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-572          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-573          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-574          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-575          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-576          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |

| Número de catálogo | Material | Product Type           | Tipo   | Works With  |
|--------------------|----------|------------------------|--------|-------------|
| 21630-192          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-257          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-564          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-577          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-131          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-132          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-133          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-193          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-194          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-195          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-196          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-197          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-258          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-259          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-565          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-566          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-567          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-568          | Acero    | Cabinet/Rack Top Cover | Closed |             |

| Número de catálogo | Material | Product Type           | Tipo   | Works With  |
|--------------------|----------|------------------------|--------|-------------|
| 21630-569          | Acero    | Cabinet/Rack Top Cover | Closed |             |
| 21630-578          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-579          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-580          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-581          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |
| 21630-582          | Acero    | Cabinet/Rack Top Cover | Closed | Varistar CP |

### ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

### ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**