

# Varistar CP Steel Door, Perforated With 1-Point Locking

## Servicios públicos de energía

Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

### CARACTERÍSTICAS

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

### ESPECIFICACIONES

Table 1/2

| Número de catálogo | Rack Height | Altura  | Ancho  | Locking Type         | Color      | Color Code |
|--------------------|-------------|---------|--------|----------------------|------------|------------|
| 21630-408          | 24 U        | 1200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-409          | 24 U        | 1200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-507          | 24 U        | 1200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-508          | 24 U        | 1200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-410          | 29 U        | 1400 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-411          | 29 U        | 1400 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-509          | 29 U        | 1400 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |

| Número de catálogo | Rack Height | Altura  | Ancho  | Locking Type         | Color      | Color Code |
|--------------------|-------------|---------|--------|----------------------|------------|------------|
| 21630-510          | 29 U        | 1400 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-412          | 33 U        | 1600 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-413          | 33 U        | 1600 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-511          | 33 U        | 1600 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-512          | 33 U        | 1600 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-414          | 38 U        | 1800 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-415          | 38 U        | 1800 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-513          | 38 U        | 1800 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-514          | 38 U        | 1800 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-006          | 42 U        | 2000 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-013          | 42 U        | 2000 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-515          | 42 U        | 2000 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-516          | 42 U        | 2000 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-007          | 47 U        | 2200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-014          | 47 U        | 2200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-517          | 47 U        | 2200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-518          | 47 U        | 2200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-008          | 52 U        | 2450 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |

| Número de catálogo | Rack Height | Altura  | Ancho  | Locking Type         | Color      | Color Code |
|--------------------|-------------|---------|--------|----------------------|------------|------------|
| 21630-015          | 52 U        | 2450 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |

Table 2/2

| Número de catálogo | Cumple con               | Product Type | Protection Rating | Tipo                   | Works With  |
|--------------------|--------------------------|--------------|-------------------|------------------------|-------------|
| 21630-408          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-409          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-507          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-508          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-410          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-411          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-509          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-510          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-412          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-413          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-511          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-512          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-414          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-415          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-513          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |

| Número de catálogo | Cumple con               | Product Type | Protection Rating | Tipo                   | Works With  |
|--------------------|--------------------------|--------------|-------------------|------------------------|-------------|
| 21630-514          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-006          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-013          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-515          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-516          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-007          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-014          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-517          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-518          | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-008          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-015          | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**