

EuropacPRO 19" Subrack Kit for Backplane, Retrofit Shielding

Servicios públicos de energía

Non-shielded subrack for backplane mounting.



CERTIFICACIONES



CARACTERÍSTICAS

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Rear horizontal rail for backplane mounting with insulation strip

Aluminum construction

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Profundidad	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-131	3 U	175 mm	1	Backplane	160 mm	Acero inoxidable
24563-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	Acero inoxidable
24563-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Acero inoxidable
24563-134	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Acero inoxidable
24563-135	3 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Acero inoxidable
24563-136	3 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Acero inoxidable
24563-431	6 U	175 mm	1	Backplane	160 mm	Acero inoxidable
24563-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	Acero inoxidable
24563-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Acero inoxidable
24563-434	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Acero inoxidable
24563-435	6 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Acero inoxidable
24563-436	6 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Acero inoxidable

Table 2/3

Número de catálogo	Handle Included	Montaje	Cumple con	EMC Shielding	Product Type	Rack Width
24563-131	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-132	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Número de catálogo	HandleIncluded	Montaje	Cumple con	EMC Shielding	Product Type	Rack Width
24563-133	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-134	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-135	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-136	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-431	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-432	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-433	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-434	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-435	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-436	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Table 3/3

Número de catálogo	Carga estática
24563-131	11 kgf
24563-132	11 kgf
24563-133	11 kgf
24563-134	11 kgf
24563-135	11 kgf
24563-136	11 kgf
24563-431	11 kgf

Número de catálogo	Carga estática
24563-432	11 kgf
24563-433	11 kgf
24563-434	11 kgf
24563-435	11 kgf
24563-436	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE