

EuropacPRO 19" Subrack Kit for DIN Connector, Slide Rail, Retrofit Shielding

Servicios públicos de energía



Non-shielded subrack for Din Connector mounting EN 60603-2 , Subrack can be assembled on slide rails to support the subrack inside a cabinet.

CERTIFICACIONES



CARACTERÍSTICAS

Subrack with side panel type F ("flexible"), 19" bracket with notch for slide rail assembly

Installed load up to 11 kg

Subrack can be used with slide rails

Horizontal rails, rear, for connector mounting (IEC 60603-2 / DIN 41612)

Threaded insert pre-fitted

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Profundidad	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-494	6 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Acero inoxidable

Número de catálogo	Rack Height	Profundidad	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-493	6 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Acero inoxidable
24553-492	6 U	235 mm	1	DIN Connector	160 mm, 220 mm	Acero inoxidable
24553-194	3 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Acero inoxidable
24553-193	3 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Acero inoxidable
24553-192	3 U	235 mm	1	DIN Connector	160 mm, 220 mm	Acero inoxidable

Table 2/3

Número de catálogo	Handle Included	Montaje	Cumple con	EMC Shielding	Product Type	Rack Width
24553-494	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-493	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-492	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-194	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-193	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-192	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Table 3/3

Número de catálogo	Carga estática
24553-494	11 kgf
24553-493	11 kgf
24553-492	11 kgf
24553-194	11 kgf

Número de catálogo	Carga estática
24553-193	11 kgf
24553-192	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE