

Guide Rail With Coding, preassembled ESD Clip for CompactPCI/ VME64x, PC

Servizi di distribuzione di energia

CARATTERISTICHE

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to an optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

ESD clip for an conductive contact between PCB and horizontal rail preassembled

Storage temperature: from -40 °C ... 130 °C

SPECIFICHE

Table 1/2

Numero catalogo	Colore	Package Quantity	Board Depth	Groove Width	È conforme a	Materiale
24568-847	Rosso	10	160 mm	2	EN 45545-2	Policarbonato
24568-848	Grigio	10	160 mm	2	EN 45545-2	Policarbonato
24568-850	Rosso	10	160 mm	2	EN 45545-2	Policarbonato
24568-851	Grigio	10	160 mm	2	EN 45545-2	Policarbonato
24568-853	Rosso	10	70 mm	2	EN 45545-2	Policarbonato

Numero catalogo	Colore	Package Quantity	Board Depth	Groove Width	È conforme a	Materiale
24568-854	Grigio	10	70 mm	2	EN 45545-2	Policarbonato
24568-855	Rosso	10	70 mm	2	EN 45545-2	Policarbonato
24568-856	Grigio	10	70 mm	2	EN 45545-2	Policarbonato

Table 2/2				
Numero catalogo	Product Family	Product Type	Tipo	Works With
24568-847	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-848	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-850	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-851	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-853	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-854	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems

Numero catalogo	Product Family	Product Type	Tipo	Works With
24568-855	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-856	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE