


# EuropacPRO 19" Subrack Kit for Power Distribution Module, Unshielded

## Servicios públicos de energía



For mounting installation devices in accordance with DIN 43880 in sizes 1-3 with snap-in technology e.g. mounting sockets, circuit breakers or residual current circuit breaker. These can be fitted after the horizontal rail with lip DIN central rail (35/7.5) are fitted.

## CERTIFICACIONES



## CARACTERÍSTICAS

For mounting installation devices in accordance with DIN 43880 in sizes 1-3 with snap-in technology e.g. mounting sockets, circuit breakers or residual current circuit breaker. These can be fitted after the horizontal rail with lip DIN central rail (35/7.5) are fitted

Modular frame to accept e.g. power distribution modules

Internal and external dimensions in accordance with the IEC 60297-3-101 and IEEE 1101.1 standards

Aluminium side panels

Horizontal rails type "light"

IEEE 1101.1 compatible

## ESPECIFICACIONES

Table 1/2

| Número de catálogo | Product Type | Rack Height | Rack Width | Profundidad | For Mounting | EMC Shielding |
|--------------------|--------------|-------------|------------|-------------|--------------|---------------|
|--------------------|--------------|-------------|------------|-------------|--------------|---------------|

|           |                 |     |       |        |                           |    |
|-----------|-----------------|-----|-------|--------|---------------------------|----|
| 24563-100 | Subrack/Chassis | 3 U | 84 HP | 115 mm | Power Distribution Module | No |
|-----------|-----------------|-----|-------|--------|---------------------------|----|

Table 2/2

| Número de catálogo | Carga estática | Handle Included | Montaje | Cumple con      | Package Quantity |
|--------------------|----------------|-----------------|---------|-----------------|------------------|
| 24563-100          | 2.5 kgf        | No              | Rack    | IEC 60297-3-103 | 1                |

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**