

T-Series Horizontal Installation Equipment



T-Series horizontal installation equipment kits contain the following: Pouring basin frame, crucible frame set (crucible chain assembly, crucible extension, crucible cover), two end alignment fittings and a horizontal packing clamp. Installation equipment kits contain components that are long lasting and often interchangeable with other sizes. Ordering installation equipment kits simplifies ordering, reduces order errors and helps ensure proper sizing of components.

CARACTERÍSTICAS

Simplifies ordering

Used to splice the same diameter bars

All components are designed for an extended life

ESPECIFICACIONES

Table 1/1

Número de catálogo	Material	Tamaño de las barras de armado, métrico
RBW73914H	Acero, Graphite	43 mm
RBW73918H	Acero, Graphite	57 mm
RBW7395H	Acero, Graphite	16 mm
RBW7396H	Acero, Graphite	20 mm
RBW7397H	Acero, Graphite	22 mm
RBW7398H	Acero, Graphite	25 mm
RBW7399H	Acero, Graphite	28 mm


Número de catálogo	Material	Tamaño de las barras de armado, métrico
RBW73910H	Acero, Graphite	32 mm
RBW73911H	Acero, Graphite	36 mm

DETALLES ADICIONALES DEL PRODUCTO

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

Components can also be purchased separately: (1) Pouring Basin Frame, (2) Crucible Chain Assembly, (3) Crucible Extension, (4) Crucible Cover, (5) End Alignment Fitting, and (6) Horizontal Packing Clamp.

DIAGRAMAS



ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

+1.800.753.9221

Opción 1: Atención al
cliente

Opción 2: Soporte técnico

Europa

Países Bajos:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Alemania:

800 1890272

Otros países:

+31 13 5835404

Asia-Pacífico

Shanghái:

+86 21 2412 1618/19

Sídney:

+61 2 9751 8500



Nuestro gran portafolio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

©2025 nVent. Todas las marcas y logotipos de nVent son propiedad de nVent Services GmbH o sus filiales, o se utilizan bajo su licencia. El resto de las marcas comerciales son propiedad de sus respectivos propietarios. nVent se reserva el derecho a cambiar las especificaciones sin previo aviso.

Este documento lo ha generado el sistema.