

# Assembly Parts for Rugged Components

## Servicios públicos de energía



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

### CERTIFICACIONES



### CARACTERÍSTICAS

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

### ESPECIFICACIONES

Table 1/2

| Número de catálogo | Tipo              | Longitud | Package Quantity | Tamaño de rosca | Material         | Product Family |
|--------------------|-------------------|----------|------------------|-----------------|------------------|----------------|
| 24566-105          | Countersunk Screw | 7 mm     | 100              | M4              | Acero inoxidable | EuropacPRO     |
| 24566-104          | Panhead Screw     | 8 mm     | 100              | M4              | Acero inoxidable | EuropacPRO     |
| 24566-106          | Countersunk Screw | 10 mm    | 100              | M4              | Acero inoxidable | EuropacPRO     |
| 24566-103          | Panhead Screw     | 10 mm    | 100              | M4              | Acero inoxidable | EuropacPRO     |

| Número de catálogo | Tipo              | Longitud | Package Quantity | Tamaño de rosca | Material         | Product Family |
|--------------------|-------------------|----------|------------------|-----------------|------------------|----------------|
| 24566-102          | Panhead Screw     | 14 mm    | 100              | M4              | Acero inoxidable | EuropacPRO     |
| 24566-101          | Countersunk Screw | 14 mm    | 100              | M4              | Acero inoxidable | EuropacPRO     |
| 24566-100          | Countersunk Screw | 18 mm    | 100              | M4              | Acero inoxidable | EuropacPRO     |
| 24560-140          | Square Nut        |          | 100              |                 | Acero inoxidable | EuropacPRO     |

Table 2/2

| Número de catálogo | Product Type | Works With |
|--------------------|--------------|------------|
| 24566-105          | Assembly Kit | Subracks   |
| 24566-104          | Assembly Kit | Subracks   |
| 24566-106          | Assembly Kit | Subracks   |
| 24566-103          | Assembly Kit | Subracks   |
| 24566-102          | Assembly Kit | Subracks   |
| 24566-101          | Assembly Kit | Subracks   |
| 24566-100          | Assembly Kit | Subracks   |
| 24560-140          | Assembly Kit | Subracks   |

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**