

Elexant 450c Control Unit



nVent RAYCHEM Elexant 450c is the next generation touch screen heat tracing controller for dual independent heating zone control, with multiple integrated sensing modes and remote alarm capability, providing the most energy efficient pipe freeze protection and temperature maintenance control system.

CARATTERISTICHE

Elexant 450c with Modbus RS485 port for remote monitoring connectivity, configuration, and ease of integration in a Building Management System (BMS).

Intuitive set-up and programming of the unit with a 4.3" color touch screen

Controls 2 independent heating circuits

Alarm relay with change over contact to signal power, temperature or communication problems

Pipe temperature monitoring with high and low temperature alarm

Heating system diagnostic data maintained in a logged file for easy download

USB port for preset-up in power off mode and firmware upgrade

Reliable during long life: 6 year extended product warranty available

SPECIFICHE

Output Relay:	2 x 4 A @ 230 VAC
Sensor Cable Length:	5 m
Profondità:	56 mm
Altezza:	110 mm
Larghezza:	158 mm
Supply Voltage:	195 - 253 V
Temperature Control Range:	0 - 85 °C
Montaggio:	Profilato DIN
Classe di protezione IP:	IP20
Sensor Type:	NTC, 2KΩ @ 25°C
Alarm Relay:	Single Pole Double Throw Relay, Voltage-free, Rating 2 A @ 250 VAC

Table 1/1

Numero catalogo	Nome articolo	Communication Protocol
1244-021970	ELEXANT 450c	Nessuno
1244-022623	ELEXANT 450c-Modbus	Modbus RTU

ADDITIONAL PRODUCT DETAILS

Temperature Control Range, (Line Sensing) can be extended to 250° using the Elexant 450 Plug-In Sensor Module and PT100 sensor

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT