

T2Red and Reflecta Self-Regulating Floor Heating System



nVent RAYCHEM T2Red and Reflecta combines a self-regulating floor heating cable with perfect heat spreading and insulation boards. Suitable for new build and renovation, they can be applied under any type of floor surface without risk of overheating. Ideal for wooden and engineered wooden floors but also for natural stone and ceramic tiles.

CARATTERISTICHE

Energy efficient and self regulating: automatically adjusts heat output, more heat near windows, less heat under furnishings

Maximum comfort with T2Reflecta insulation board: heat spreads perfectly over the entire room

Simple, fast installation: cut-to-length, no cold leads, If combined with Reflecta then pre-grooves serve as cable fixing tool and guarantee perfect cable distance of 100-200 or 300mm spacing, suitable for all sub-floors and floor coverings, meter markings, user-friendly connections kits

Safe and efficient operation: fast heat up, uniform temperatures across the room, flexible power output from 35-100W/m², closer loops for higher output and wider loops for lower output, no overheating

Reliable during long life: 12 to 20 year total care warranty available, no maintenance required

Advanced control options available

SPECIFICHE

Table 1/3

Codice a catalogo	Nome articolo	Tecnologia del cavo di riscaldamento	Tensione nominale	Uscita alimentazione	Potenza di uscita, tipica	Materiale rivestimento esterno
948739-000	T2-RED	Autoregolante	230 V	5 – 15 W/m	80 – 125 W/m ²	Fluoropolimero

Table 2/3

Codice a catalogo	Nome articolo	Colore	Tipo di percorso a terra	Temperatura di installazione minima	Larghezza nominale	Altezza nominale

948739-000	T2-RED	Rosso	Treccia	5 °C	8.5 mm	5.8 mm
------------	--------	-------	---------	------	--------	--------

Table 3/3

Codice a catalogo	Nome articolo	Peso cavo nominale	Lunghezza massima del circuito	Interruttore automatico
948739-000	T2-RED	68 g/m	100 m	Tipo C/10 Amp

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Il nostro straordinario portafoglio di marchi:

RAYCHEM PYROTENAX TRACER NUHEAT