

XL-Trace Pre-Terminated, Low Smoke Zero Halogen Self-Regulating Cable Kit



nVent RAYCHEM kits comprise a 10XL2-ZH self-regulating heating cable with a pre-installed low smoke zero halogen cold lead cable of 4 m, cold lead to heater cable splice and end seal. The kits are available in fixed lengths between 3-30 m. Factory terminated and electrically tested.

CARATTERISTICHE

Unparalleled safety, low smoke zero halogen construction: up to 90% less smoke emissions and improved self-extinguishing properties

Energy efficient: self-regulating cable, major savings when used with proportional ambient sensing controller (PASC), no cable overheating possible

Easy to install, pre-terminated kits

Zero halogen: IEC60754-1 tested and compliant

Improved self-extinguishing properties under the IEC62395 flammability test

SPECIFICHE

Cold Lead Length:	4 m
Nominal Height:	6,8 mm
Nominal Power Output @ 5°C, 230V:	10 W/m
Nominal Width:	13,8 mm
Max Continuous Exposure Temperature, Power On:	65 °C
Supply Voltage:	220 - 240 V
Temperatura minima di installazione:	-40 °C
Ground Path Type:	e collegamento
Outer Jacket Material:	Low Smoke Zero Halogen
Colore:	Plum
Heating Cable Technology:	Self-Regulating

Table 1/1

Numero catalogo	Nome articolo	Lunghezza
1244-021271	10XL2-ZH-KIT-3m	3 m
1244-021272	10XL2-ZH-KIT-5m	5 m
1244-021273	10XL2-ZH-KIT-8m	8 m
1244-021274	10XL2-ZH-KIT-12m	12 m
1244-021275	10XL2-ZH-KIT-16m	16 m
1244-021276	10XL2-ZH-KIT-20m	20 m
1244-021277	10XL2-ZH-KIT-25m	25 m
1244-021278	10XL2-ZH-KIT-30m	30 m

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT