


Plug-In Unit Kit for FMC, Chromated, Shielded (Textile) With Handle



The FMC bezel are in accordance with Vita 57.1 specification. Covers the cut out in the overall front panel.

CERTIFICAZIONI



CARATTERISTICHE

In accordance with Vita 57.1 specification

For single 69.0 x 76.5 mm or double 139.0 x 76.5 mm modules

Al-Profile plug-in unit with IEL handle

SPECIFICHE

Larghezza rack:	4HP
Materiale:	Alluminio
Finitura:	Anodizzato; Passivato
Tipo di prodotto:	Pannello frontale

Tipo: Pannello frontale con maniglia (PIU)

Schermatura EMC: Sì

Table 1/2

Codice a catalogo	Altezza del rack	Quantità nella confezione	Tipo di maniglia	Montaggio	Tipo di guarnizione EMC	Finitura anteriore
20836-253	3U	1	IEL	Anteriore a vite	Tessuto	Anodizzato
20836-254	6U	1	IEL	Anteriore a vite	Tessuto	Anodizzato

Table 2/2

Codice a catalogo	Finitura posteriore	Bordi trattati	È conforme a	Altezza	Larghezza	Spedizione rapida
20836-253	Conduttivo	No	FMC Mezzanine, Vita 57,1	128.4mm	20mm	No
20836-254	Conduttivo	No	FMC Mezzanine, Vita 57,1	261.8mm	20mm	No

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE