


Guide Rail Accessories for Heavy PCBs, Extra Strong

Servizi di distribuzione di energia



This reinforced guide rail for heavy PCBs of the type accessory, forms a reliable interface between the subrack mechanics and the sub-assemblies. The guide rails can additionally be bolted to the horizontal

CERTIFICAZIONI



CARATTERISTICHE

For especially heavy PCBs, plug-in units or frame type plug-in units

Mounting, for bolting to type H (heavy) and type R (rugged) horizontal rails only

Aluminium profile

SPECIFICHE

Table 1/2

Numero catalogo	Board Depth	Groove Width	Colore	Materiale	Product Family	Product Type
-----------------	-------------	--------------	--------	-----------	----------------	--------------

34562-884	340 mm	2	Silver	Alluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-885	400 mm	2	Silver	Alluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-881	160 mm	2	Silver	Alluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-883	280 mm	2	Silver	Alluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-882	220 mm	2	Silver	Alluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-881	160 mm	2.5	Silver	Alluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail

34564-882	220 mm	2.5	Silver	Alluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-883	280 mm	2.5	Silver	Alluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-884	340 mm	2.5	Silver	Alluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-885	400 mm	2.5	Silver	Alluminio	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail

Table 2/2

Numero catalogo	Tipo	Works With
34562-884	Per applicazioni pesanti	Subracks, Cases, Chassis
34562-885	Per applicazioni pesanti	Subracks, Cases, Chassis
34562-881	Per applicazioni pesanti	Subracks, Cases, Chassis
34562-883	Per applicazioni pesanti	Subracks, Cases, Chassis
34562-882	Per applicazioni pesanti	Subracks, Cases, Chassis

Numero catalogo	Tipo	Works With
34564-881	Per applicazioni pesanti	Subracks, Cases, Chassis
34564-882	Per applicazioni pesanti	Subracks, Cases, Chassis
34564-883	Per applicazioni pesanti	Subracks, Cases, Chassis
34564-884	Per applicazioni pesanti	Subracks, Cases, Chassis
34564-885	Per applicazioni pesanti	Subracks, Cases, Chassis

ADDITIONAL PRODUCT DETAILS

Delivery is exclusively in standard pack quantity.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE