

# Interscale Mounting Plate With Built-In Fan Holder and Fans

## Servizi di distribuzione di energia

Interscale mounting plate with built-in fan holder and fans, for desktop cases and 19" chassis. Available in different sizes and with three fan versions, with a air flow volume from 10 to 170 m3/h.

### CARATTERISTICHE

Mounting plate (raised 4 mm) with integrated fan holder including fan kit for perforated case versions

Fans are simple to fit to the mounting plate using vibrationdamping fixing material

Mounting plate fixes into desktop case with 4 plastic feet or into 19" case with 4 screws

For technical data of fans, please see delivery includes

### SPECIFICHE

Table 1/2

| Numero catalogo | Larghezza | Profondità | Altezza | Materiale | Product Family | Product Type   |
|-----------------|-----------|------------|---------|-----------|----------------|----------------|
| 24827-105       | 444 mm    | 177 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-107       | 444 mm    | 310 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-154       | 221 mm    | 177 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-155       | 221 mm    | 221 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-175       | 310 mm    | 221 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-195       | 399 mm    | 221 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-197       | 399 mm    | 310 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |

| Numero catalogo | Larghezza | Profondità | Altezza | Materiale | Product Family | Product Type   |
|-----------------|-----------|------------|---------|-----------|----------------|----------------|
| 24827-255       | 221 mm    | 221 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-275       | 310 mm    | 221 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-295       | 399 mm    | 221 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-297       | 399 mm    | 310 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-375       | 310 mm    | 221 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-395       | 399 mm    | 221 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-397       | 399 mm    | 310 mm     | 1 mm    | Acciaio   | Interscale     | Mounting Plate |
| 24827-254       |           |            |         |           | Interscale     | Mounting Plate |
| 24827-205       |           |            |         |           |                | Mounting Plate |
| 24827-207       |           |            |         |           |                | Mounting Plate |
| 24827-305       |           |            |         |           |                | Mounting Plate |
| 24827-307       |           |            |         |           |                | Mounting Plate |

Table 2/2

| Numero catalogo | Rack Width | Tipo           | Works With              |
|-----------------|------------|----------------|-------------------------|
| 24827-105       | 19 HP      | Mounting Plate | Small Form Factor Cases |
| 24827-107       | 19 HP      | Mounting Plate | Small Form Factor Cases |
| 24827-154       |            | Mounting Plate | Small Form Factor Cases |
| 24827-155       |            | Mounting Plate | Small Form Factor Cases |
| 24827-175       |            | Mounting Plate | Small Form Factor Cases |

| Numero catalogo | Rack Width | Tipo           | Works With              |
|-----------------|------------|----------------|-------------------------|
| 24827-195       |            | Mounting Plate | Small Form Factor Cases |
| 24827-197       |            | Mounting Plate | Small Form Factor Cases |
| 24827-255       |            | Mounting Plate | Small Form Factor Cases |
| 24827-275       |            | Mounting Plate | Small Form Factor Cases |
| 24827-295       |            | Mounting Plate | Small Form Factor Cases |
| 24827-297       |            | Mounting Plate | Small Form Factor Cases |
| 24827-375       |            | Mounting Plate | Small Form Factor Cases |
| 24827-395       |            | Mounting Plate | Small Form Factor Cases |
| 24827-397       |            | Mounting Plate | Small Form Factor Cases |
| 24827-254       |            | Mounting Plate |                         |
| 24827-205       |            |                |                         |
| 24827-207       |            |                |                         |
| 24827-305       |            |                |                         |
| 24827-307       |            |                |                         |

## AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**