

RackPower PDU, RP6xxx, 230/400 VAC, 3-phase

Servizi di distribuzione di energia

Modular, compact intelligent PDU with inlet metering and remote outlet switching. Ultra-Low Profile Design with only 50 mm height.

CARATTERISTICHE

RackPower RP6xxx Intelligent Power Distribution Units monitors input and outlet power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6", with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

User-defined power-on time delay or automatic power-on sequencing

SPECIFICHE

Table 1/2

Numero catalogo	Product Type	Socket Type	Colore	Lunghezza	Voltage AC	Function
RP6950	Socket Strip	IEC C13, IEC C13/C19	Nero	1826 mm	230 V	Input Monitored, Outlet Monitored, Switched Outlets

Numero catalogo	Product Type	Socket Type	Colore	Lunghezza	Voltage AC	Function
RP6850	Socket Strip	IEC C13, IEC C13/C19	Nero	1780 mm	230 V	Input Monitored, Outlet Monitored, Switched Outlets
RP6450	Socket Strip	IEC C13, IEC C13/C19	Nero	1490 mm	230 V	Input Monitored, Outlet Monitored, Switched Outlets

Table 2/2

Numero catalogo	Profondità	Larghezza
RP6950	75 mm	56 mm
RP6850	75 mm	56 mm
RP6450	75 mm	56 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE