

Varistar CP Plain Steel Door, Seismic IP55, With Multi-Point Locking

Servizi di distribuzione di energia

IP55 Seismic Steel Door with lever handle and multi-Point locking.

CARATTERISTICHE

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for EMC applications

SPECIFICHE

Table 1/3

Numero catalogo	Rack Height	Altezza	Larghezza	Colore	Color Code	È conforme a
21630-752	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-753	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-754	38 U	600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-2, IEC 61587-2, IEC 60529
21630-755	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-756	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-757	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

Numero catalogo	Rack Height	Altezza	Larghezza	Colore	Color Code	È conforme a
21630-758	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-759	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

Table 2/3

Numero catalogo	Locking Type	Materiale	Product Type	Protection Rating	Rack Width	Tipo
21630-752	4-Point Locking	Acciaio	Cabinet Door	IP55		Steel Door, Plain
21630-753	4-Point Locking	Acciaio	Cabinet Door	IP55	800 HP	Steel Door, Plain
21630-754	4-Point Locking	Acciaio	Cabinet Door	IP55		Steel Door, Plain
21630-755	4-Point Locking	Acciaio	Cabinet Door	IP55		Steel Door, Plain
21630-756	4-Point Locking	Acciaio	Cabinet Door	IP55		Steel Door, Plain
21630-757	4-Point Locking	Acciaio	Cabinet Door	IP55		Steel Door, Plain
21630-758	5-Point Locking	Acciaio	Cabinet Door	IP55		Steel Door, Plain
21630-759	5-Point Locking	Acciaio	Cabinet Door	IP55		Steel Door, Plain

Table 3/3

Numero catalogo	Works With
21630-752	Varistar CP
21630-753	Varistar CP
21630-754	Varistar CP
21630-755	Varistar CP
21630-756	Varistar CP

Numero catalogo	Works With
21630-757	Varistar CP
21630-758	Varistar CP
21630-759	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE