

HWAT-T55 Thermostat



nVent RAYCHEM HWAT-T55 is an energy efficient thermostat for use in nVent RAYCHEM HWAT self-regulating single pipe hot water systems, in small pipe networks or for branch lines.

CARATTERISTICHE

Simple to install and operate: digital display for temperature and alarm, 35 mm DIN-Rail mountable

Energy saving: 3 operating modes ON/ECO/OFF; with HWAT-L the system can be switched ON/OFF during absence periods, with HWAT-M/R there are three preset temperatures 55/50/45 °C, integrated clock and energy savings (ECO) for off-peak usage

System monitoring through high temperature alarm: if a temperature over 66 °C is measured the system will be switched off to avoid scalding and calcification

System monitoring through low temperature alarm: to avoid unnecessary energy consumption when hot water storage problems occur

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICHE

Table 1/2

Numero catalogo	Nome articolo	Classe di protezione IP	Voltage Rating	Voltage Rating Type	Adjustment Range	Nominal Switching Current @ 250V, Potential Free
1244-015722	HWAT-T55	IP20	195 – 253 V	AC	40 – 60 °C	16 A

Table 2/2

Numero catalogo	Nome articolo	Power Consumption, Standby	Altezza	Larghezza	Profondità

1244-015722	HWAT-T55	5 W	87.5 mm	52.5 mm	87.5 mm
-------------	----------	-----	---------	---------	---------

ADDITIONAL PRODUCT DETAILS

The nVent RAYCHEM HWAT-T55 thermostat is designed for use with HWAT-L, -M or -R. Maximum circuit length is limited to 50 m. For temperature adjustment, consider local hygienic standards.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT