

Junction Box for Non-Hazardous Industrial Locations



nVent RAYCHEM Junction Boxes for non hazardous area are designed to connect power to up to one or three RAYCHEM BSA, BTV, QTVR, XTV, KTV or VPL industrial parallel heating cables. They are part of a modular component system; it allows for maximum flexibility and can be either wall or pipe mounted. Connection kits (M25) and insulation entry kits have to be ordered separately.

CARATTERISTICHE

Fast installation

Spacious box with front access

Captive lid screws, cannot be lost during installation

Robust spring type terminals for fast and secure fixing

Reliable operation

Heavy-duty glass reinforced polymer

Weather proof IP66

10 year product warranty extension

SPECIFICHE

Materiale:	Glass Fiber Reinforced Polymer
Classe di protezione IP:	IP66
Area Classification:	Non-Hazardous
Montaggio:	Wall/Support Bracket Mounted
Ambient Temperature:	da -40 a 90 °C
Voltage Rating:	Max 800 V

Table 1/2

Numero catalogo	Nome articolo	Inlet Quantity	Max Conductor Cross Section Stranded	Max Conductor Cross Section Solid	Altezza	Larghezza
-----------------	---------------	----------------	--------------------------------------	-----------------------------------	---------	-----------

1244-020910	JB-NH2	2	4 mm ²	6 mm ²	75 mm	110 mm
1244-020911	JB-NH4	4	4 mm ²	6 mm ²	120 mm	120 mm

Table 2/2

Numero catalogo	Nome articolo	Profondità	Light Indication Included	Earth Plate Included
1244-020910	JB-NH2	75 mm	No	No
1244-020911	JB-NH4	90 mm	No	No

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT