

NRG-DM Digital Timer Thermostat



nVent RAYCHEM NRG-DM is a digital timer thermostat for electrical floor heating equipped with a large display and intuitive software. Eco Design compliant thanks to the following functions: Adaptive start control. For more details, please consult the Commissioning sheet (INST324 or EU2550).

CARATTERISTICHE

Easy to use, intuitive navigation: large LCD display with blue back light

3 operating modes: event mode or weekly schedule to reduce energy; boost mode or temporary override; constant mode

Energy efficient adaptive function

Optimum heat management, with 4 sensor modes

Reliable during long life: 12 year total care warranty available, maintenance free

SPECIFICHE

Table 1/5

Numero catalogo	Nome articolo	Power Supply	Measuring Range	Adjustable Differential	Regulation Type	Max Contact Voltage
1244-015152	R-NRG-DM	230 V	5 – 40 °C	No	On/Off	230 V

Table 2/5

Numero catalogo	Nome articolo	Max Contact Load	Sensor/Feeler Type	Temperature Control Class	Control Characteristic	Remote Operation
1244-015152	R-NRG-DM	13 A	Resistance Sensor	IV	PID	No

Table 3/5

Numero catalogo	Nome articolo	Switching Program Quantity	Power Consumption, Standby	Classe di protezione IP	RAL Number	Colore

1244-015152	R-NRG-DM	7	0.4 W	IP21	9010	Clear White
-------------	----------	---	-------	------	------	-------------

Table 4/5

Numero catalogo	Nome articolo	IFTTT Support Available	Clock Type	Clock Model	Self Learning	Altezza
1244-015152	R-NRG-DM	No	Day Clock	Digitale	Sì.	82 mm

Table 5/5

Numero catalogo	Nome articolo	Larghezza	Profondità
1244-015152	R-NRG-DM	82 mm	40 mm

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT