

Polymer Junction Box For PI Cables



nVent RAYCHEM JB-EX-XX are junction boxes with or without earth plate and external earth stud. Depending on the type, they are equipped with 10 mm² or 35 mm² terminals to allow loads up to 100 A to a power supply or other configurations such as Tees or Splices. Available in different sizes with a various number of M20 entries to accommodate multiple configurations and electrical loads.

CARATTERISTICHE

Simple and fast to install, easy to maintain

Hazardous areas approved

Available in different models and sizes for multiple configurations

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICHE

Area Classification:	Non-Hazardous; Hazardous
Classe di protezione IP:	IP66
Montaggio:	Wall/Support Bracket Mounted
Ambient Temperature:	da -55 a 55 °C

Table 1/2

Numero catalogo	Nome articolo	Max Voltage	Cable Entry	Max Conductor Cross Section	Altezza	Larghezza
1244-006384	JB-EX-20-EP	590 V	1xM25 3xM20	10 mm ²	120 mm	122 mm
1244-000579	JB-EX-21	550 V	1xM32 6xM20	10 mm ²	160 mm	160 mm
1244-000590	JB-EX-20	590 V	1xM25 3xM20	10 mm ²	120 mm	122 mm
1244-006653	JB-EX-21/35MM2	690 V	1xM40 6xM20	35 mm ²	160 mm	260 mm

Table 2/2

Numero catalogo	Nome articolo	Profondità	Light Indication Included	Earth Plate Included
1244-006384	JB-EX-20-EP	90 mm	No	Sì.
1244-000579	JB-EX-21	90 mm	No	No
1244-000590	JB-EX-20	90 mm	No	No
1244-006653	JB-EX-21/35MM2	90 mm	No	No

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT