

TCONTROL-05 Electronic Controller



nVent RAYCHEM TCONTROL-05 is a family of single circuit electronic temperature controllers for non-hazardous areas. Most often this controller is installed in panels. Various versions of this controller are available, see datasheet for more details. Each can be used in combination with any PT100 temperature sensor or standard thermocouples. The temperature range is from -200 to 2400 °C, depending on the type of temperature sensor used.

CARATTERISTICHE

Easy to install, program and operate: display indicates the process value and the set point, during programming it also provides guidance to simplify commissioning, service counters record and eventually alarm on the number of relay operations

Easy to use RAYCHEM TCONTROL-05/CONFIG software can optionally be used for computer aided configuration

Robust, compact and space saving

Adjustable set point: -200 °C to +2400 °C, depending on temperature sensor

Time-delay after initial power up: can be used to avoid peak demands on power during start-up

Input temperature sensors are permanently monitored for failures

SPECIFICHE

Altezza:	48 mm
Larghezza:	48 mm
Profondità:	78 mm
Voltage Rating:	110 - 240 V
Temperatura di esercizio:	da -10 a 55 °C

Table 1/1

Numero catalogo	Nome articolo	Communication Protocol	4-20 mA Temperature Input
1244-022499	TCONTROL-05/COM	Modbus RTU	No
1244-022498	TCONTROL-05/COMA	Modbus RTU	Sì.

Numero catalogo	Nome articolo	Communication Protocol	4-20 mA Temperature Input
1244-022496	TCONTROL-05	Nessuno	No
1244-022497	TCONTROL-05/MA	Nessuno	Sì.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT