


Aardingsklem voor waterpijp



The nVent ERICO Water Pipe Ground Clamp provides a highly reliable method for grounding copper conductors to metallic water pipes or ground rods, essential for electrical safety in residential, commercial, and industrial systems. Constructed from high-strength silicone bronze, this clamp ensures excellent durability, corrosion resistance, and secure, long-lasting electrical connections. Its robust design makes it a trusted component for creating effective grounding paths in accordance with applicable electrical codes and standards.

CERTIFICERINGEN



KENMERKEN

Zeer sterk siliciumbrons

Gebruikt voor het aansluiten van koperen geleiders op metalen waterleidingen of aardingsstangen.

Designed for effectively connecting copper conductors to metallic water pipes or ground rods

Ensures a secure and low-resistance path for grounding applications

Suitable for a range of conductor and pipe sizes

SPECIFICATIES


Materiaal: Siliciumbrons

Table 1/1

Catalogusnummer	Artikelnummer	Buisafmeting, nominaal (Ø)	Buisafmeting, werkelijk (Ø)	Certificeringen
CWP1JJ	710262	1/2" - 1"	12.7 - 25.4 mm	
CWP1JU	710266	1/2" - 1"	12.7 - 25.4 mm	CSA, UL, cUL

Catalogusnummer	Artikelnummer	Buisafmeting, nominaal (Ø)	Buisafmeting, werkelijk (Ø)	Certificeringen
CWP4J	710264	2 1/2" - 4"	63.5 - 101.6 mm	CSA, UL, cUL

DIAGRAMMEN



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

Noord-Amerika

+1.800.753.9221
optie 1 – Klantenservice
optie 2 – Technische
ondersteuning

Europa

Nederland:
+31 800-0200135
Frankrijk:
+33 800 901 793

Europa

Duitsland:
800 1890272
andere landen:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE