

## Sivusokkeli | Lattiakaapit, PS



The extra space created by the plinth is closed off by using these panels in order to restrict access to this area.

### FEATURES

---

Description: Side panels to cover the openings in the sides of the PF/PV plinths. Double folded panels for maximum strength. Compatible with combinable and semi-compact enclosure ranges.

Material: 1.5 mm steel plate.

Finish: RAL 7022 structured powder coating.

Pack quantity: 2 panels. Mounting accessories included with PF/PV.

## SPECIFICATIONS

**Thickness:** 1.5mm  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7022  
**Color:** Umbra Gray

Table 1/1

| Catalog Number | Height | Width | Depth | Enclosure Material | Product Family | Quick Ship |
|----------------|--------|-------|-------|--------------------|----------------|------------|
| PS1030         | 100mm  | 300mm | 27mm  | Mild Steel         | Free-Standing  | No         |
| PS1050         | 100mm  | 500mm | 27mm  | Mild Steel         | Free-Standing  | No         |
| PS2050         | 200mm  | 500mm | 27mm  | Mild Steel         | Free-Standing  | No         |
| PS1040         | 100mm  | 400mm | 27mm  | Mild Steel         | Free-Standing  | No         |
| PS2040         | 200mm  | 400mm | 27mm  | Mild Steel         | Free-Standing  | No         |
| PS1060         | 100mm  | 600mm | 27mm  | Mild Steel         | Free-Standing  | No         |
| PS2060         | 200mm  | 600mm | 27mm  | Mild Steel         | Free-Standing  | No         |
| PS1080         | 100mm  | 800mm | 27mm  | Mild Steel         | Free-Standing  | No         |
| PS2080         | 200mm  | 800mm | 27mm  | Mild Steel         | Free-Standing  | No         |
| PS2030         | 200mm  | 300mm | 27mm  | Mild Steel         | Free-Standing  | No         |
| PS1100         | 100mm  | 999mm | 27mm  | Mild Steel         | Free-Standing  | No         |
| PS2100         | 200mm  | 999mm | 27mm  | Mild Steel         | Free-Standing  | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**