

Sivusokkelit, PSS



These plinth side panels close off the extra space underneath the enclosure if needed.

FEATURES

Description: Side panels to cover the openings in the sides of the PFS plinth. Double folded panels for maximum strength. Compatible with combinable and compact stainless steel floor standing ranges.

Material: AISI 304 / AISI 316L pre-grained stainless steel. Panels: 1.5 mm.

Finish: 400 pre-grained stainless steel.

Pack quantity: 2 panels. Mounting accessories included with PFS.

SPECIFICATIONS

Table 1/1						
Catalog Number	Height	Width	Depth	Enclosure Material	Product Family	Material
PSS1040	100mm	400mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 304
PSS2040	200mm	400mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 304
PSS1050	100mm	500mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 304
PSS2050	200mm	500mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 304
PSS1060	100mm	600mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 304
PSS2060	200mm	600mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 304
PSS1040-316	100mm	400mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 316
PSS1050-316	100mm	500mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 316
PSS1060-316	100mm	600mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 316
PSS2040-316	200mm	400mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 316
PSS2050-316	200mm	500mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 316
PSS2060-316	200mm	600mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 316
PSS1080-316	100mm	800mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 316
PSS1100-316	100mm	999mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 316
PSS2080-316	200mm	800mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 316
PSS2100-316	200mm	999mm	27mm	Mild Steel, Stainless Steel	Free-Standing	Stainless Steel 316

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE