


Mounting Plate for 19" Case and Subrack

Power Utilities



Mounting plate for heavy components or proprietary electronic assemblies. Suitable for RatiopacPRO/-AIR, CompacPRO and EuropacPRO.

Guide rails Type 4,4" and type strengthened cannot be used in combination with a mounting plate. Top / bottom cover which will be inserted into the groove of the light (type L) horizontal rails cannot be used in combination with a mounting plate.

CERTIFICERINGEN



KENMERKEN

For assembly of heavy components

Mounting plate, full width: The mounting plate is as wide as the subrack/system case and is fixed to the side panels

Mounting plate, partial width: The partial width mounting plate fixed to the side panel by means of an assembly strip

The chassis plate can't be combined with EMC top- / bottom covers

SPECIFICATIES

Table 1/2

Catalogusnummer	Rekbreedte	Pakkethoeveelheid	Diepte	Materiaal	Productfamilie	Producttype
34562-759	63 HP	1	292.2 mm	Aluminium	EuropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-745	28 HP	1	112.5 mm	Aluminium	EuropacPRO, RatiopacPRO, CompacPRO	Montageplaat

Catalogusnummer	Rekbreedte	Pakkethoeveelheid	Diepte	Materiaal	Productfamilie	Producttype
34562-754	42 HP	1	232.5 mm	Aluminium	EuropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-871	84 HP	1	412.5 mm	Aluminium	EuropacPRO	Montageplaat
34562-755	63 HP	1	232.5 mm	Aluminium	EuropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-870	84 HP	1	352.5 mm	Aluminium	EuropacPRO	Montageplaat
34562-746	42 HP	1	112.5 mm	Aluminium	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-753	28 HP	1	232.5 mm	Aluminium	EuropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-748	84 HP	1	112.5 mm	Aluminium	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-757	28 HP	1	292.2 mm	Aluminium	EuropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-747	63 HP	1	112.5 mm	Aluminium	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-760	84 HP	1	292.5 mm	Aluminium	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-756	84 HP	1	232.5 mm	Aluminium	EuropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-749	28 HP	1	172.5 mm	Aluminium	EuropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-751	63 HP	1	172.5 mm	Aluminium	EuropacPRO, RatiopacPRO, CompacPRO, PropacPRO	Montageplaat

Catalogusnummer	Rekbreedte	Pakkethoeveelheid	Diepte	Materiaal	Productfamilie	Producttype
34562-758	42 HP	1	292.2 mm	Aluminium	EuropacPRO, RatiopacPRO, CompacPRO	Montageplaat
34562-750	42 HP	1	172.5 mm	Aluminium	EuropacPRO, CompacPRO, RatiopacPRO, PropacPRO	Montageplaat
34562-752	84 HP	1	172.5 mm	Aluminium	EuropacPRO, CompacPRO, RatiopacPRO, PropacPRO	Montageplaat

Table 2/2

Catalogusnummer	Breedte	Werkt met	Certificeringen
34562-759	324.67 mm	Subracks	RoHS
34562-745	146.88 mm	Subracks	RoHS
34562-754	217.99 mm	Subracks	RoHS
34562-871	431.35 mm	Subracks	
34562-755	324.67 mm	Subracks	RoHS
34562-870	431.35 mm	Subracks	
34562-746	217.99 mm	Subracks	RoHS
34562-753	146.88 mm	Subracks	RoHS
34562-748	324.67 mm	Subracks	RoHS
34562-757	146.88 mm	Subracks	RoHS
34562-747	324.67 mm	Subracks	RoHS
34562-760	431.35 mm	Subracks	RoHS

Catalogusnummer	Breedte	Werkt met	Certificeringen
34562-756	431.35 mm	Subracks	RoHS
34562-749	146.88 mm	Subracks	RoHS
34562-751	324.67 mm	Subracks	RoHS
34562-758	217.99 mm	Subracks	RoHS
34562-750	217.99 mm	Subracks	RoHS
34562-752	431.35 mm	Subracks	RoHS

AANVULLENDE PRODUCTGEGEVENS

Please order assembly kit for mounting plate separately.

Other versions on request.

Fixing strips required for partial width, please order separately.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE