

Novastar Frame, Slim-Line

Energiebedrijven



Aesthetic aluminum die-cast frame with 200kg static load capacity. Aluminum extruded 19" upright bolted onto the frames.

CERTIFICERINGEN



KENMERKEN

Static load-carrying capacity 200 kg

19" plane - 33 mm at front, 60 mm at rear

Al profile, RAL 7021, incl. grounding

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Height	Hoogte	Breedte	Diepte	Kleur	Color Code
-----------------	-------------	--------	---------	--------	-------	------------

28230-001	6 U	323 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-060	6 U	323 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-004	9 U	456 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-063	9 U	456 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-007	12 U	589 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-054	12 U	589 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-055	12 U	589 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-066	12 U	589 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-126	12 U	589 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-011	16 U	767 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-070	16 U	767 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-130	16 U	767 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-190	16 U	767 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-191	16 U	767 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-015	20 U	945 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-074	20 U	945 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-134	20 U	945 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-194	20 U	945 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-195	20 U	945 mm	553 mm	1000 mm	Black Grey	RAL 7021

28230-020	25 U	1167 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-079	25 U	1167 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-139	25 U	1167 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-198	25 U	1167 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-199	25 U	1167 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-029	34 U	1567 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-088	34 U	1567 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-148	34 U	1567 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-202	34 U	1567 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-203	34 U	1567 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-033	38 U	1745 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-092	38 U	1745 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-152	38 U	1745 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-206	38 U	1745 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-207	38 U	1745 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-048	43 U	1967 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-097	43 U	1967 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-157	43 U	1967 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-210	43 U	1967 mm	553 mm	900 mm	Black Grey	RAL 7021

28230-211	43 U	1967 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-042	47 U	2145 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-101	47 U	2145 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-162	47 U	2145 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-214	47 U	2145 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-215	47 U	2145 mm	553 mm	1000 mm	Black Grey	RAL 7021

Table 2/2

Catalogusnummer	Frame Material	Product Type	Statische belasting	Type
28230-001	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-060	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-004	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-063	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-007	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-054	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-055	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-066	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-126	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-011	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-070	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-130	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line

Catalogusnummer	Frame Material	Product Type	Statische belasting	Type
28230-190	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-191	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-015	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-074	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-134	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-194	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-195	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-020	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-079	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-139	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-198	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-199	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-029	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-088	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-148	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-202	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-203	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-033	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line

Catalogusnummer	Frame Material	Product Type	Statische belasting	Type
28230-092	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-152	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-206	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-207	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-048	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-097	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-157	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-210	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-211	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-042	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-101	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-162	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-214	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-215	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line

ADDITIONAL PRODUCT DETAILS

Please order doors, rear panels, side panels, top cover assemblies, plinths, floors, shelves, slide rails and castors or adjustable feet separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of

fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.