

Varistar CP EMC Cabinet, IP 55

Energiebedrijven



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

KENMERKEN

Shielding 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3)

Shielding 30 dB at 18 GHz, (tested to EN 61000-5-7) with EN45545 gaskets

Type of protection IP 55

Static load-carrying capacity 1600 kg

Doors with 4-point locking and screw-fixed side panels

Side and rear panels can be installed by one person

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Hoogte	Frame Color	Breedte	Frame Color Code	Cladding Material
10630-043	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Staal
10630-044	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Staal

Table 2/3

Catalogusnummer	Diepte	Cladding Color	Cladding Color Code	Voldoet aan	Frame Material	Product Type
-----------------	--------	----------------	---------------------	-------------	----------------	--------------

10630-043	800 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Staal	Cabinet
10630-044	800 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Staal	Cabinet

Table 3/3

Catalogusnummer	Protection Rating	Statische belasting
10630-043	IP55	1600 kgf
10630-044	IP55	1600 kgf

ADDITIONAL PRODUCT DETAILS

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE